



# FLEET MANAGEMENT Power tool guide

MARCH 2026



### Maximize productivity

and efficiency across your projects by eliminating steps, speeding up tasks, and streamlining workflows from start to finish with Hilti's products and solutions.



You can contact us at:  
02-099-5300  
moth@hilti.com

## Cordless tools & essentials

### ROTARY HAMMERS



Material Number	3870713
Model	TE 2-22
Description	Cordless Rotary Hammer SDS Plus



ATC

Material Number	3870714
Model	TE 4-22
Description	Cordless Rotary Hammer SDS Plus



ATC

Material Number	3870715
Model	TE 6-22
Description	Cordless Rotary Hammer SDS Plus

### COMBIHAMMERS



ATC

Material Number	3870716
Model	TE 30-22
Description	Cordless Combihammer SDS Plus



ATC

Material Number	3870717
Model	TE 60-22
Description	Cordless Combihammer SDS Max

### BREAKERS



Material Number	3870719
Model	TE 500-22
Description	Cordless Breaker 5kg SDS Max



Material Number	3870720
Model	TE 2000-22
Description	Cordless Breaker 20kg TE-S end

### IMPACT WRENCHES



Material Number	2291205
Model	SIW 4AT-22
Description	Cordless impact wrenches 1/2"



Material Number	2365081
Model	SIW 6AT-22
Description	Cordless impact wrenches 1/2"



Material Number	2251627
Model	SIW 8-22
Description	Cordless impact wrenches 1/2"



Material Number	2361530
Model	SIW 10-22
Description	Cordless impact wrenches 3/4"



Material Number	2363677
Model	SIW 4R-22
Description	Right-angled impact wrenches 3/8"



Material Number	2291198
Model	SI-AT-22
Description	Adaptive torque module

### DRILL DRIVERS



ATC

Material Number	2253850
Model	SF 4H-22
Description	Cordless drill driver



ATC

Material Number	2254885
Model	SF 6H-22
Description	Cordless hammer drill driver



AVR

Material Number	2360542
Model	SF 8M-22
Description	Cordless hammer drill driver

## IMPACT DRIVERS



Material Number	2247391
Model	SID 6-22
Description	Cordless impact driver

## ANGLE GRINDERS



Material Number	3905418
Model	AG 4S-22
Description	Cordless angle grinder 4"



Material Number	3915063
Model	AG 6D-22
Description	Cordless angle grinder 5"

## SAWS



Material Number	3905395
Model	SR 6-22
Description	Reciprocating saw



Material Number	3905397
Model	SR 4-22
Description	Reciprocating saw



Material Number	2351364
Model	SC 4MR-22
Description	Metal cutting circular saw 5-3/8"



Material Number	2315445
Model	SC 6ML-22
Description	Metal cutting circular saw 6.5"



Material Number	2326030
Model	SC 6WL-22
Description	Wood cutting circular saw 6.5"



Material Number	2251185
Model	SJD 6-22
Description	Jig saw



Material Number	2366392
Model	SMT 6-22
Description	Multi-Tool

## DIE GRINDERS



Material Number	2267026
Model	GDG 6-22
Description	Die grinder

## METAL NIBBLERS



Material Number	2252738
Model	SPN 6-22
Description	Metal Nibbler

## THREADED ROD CUTTERS



Material Number	2361757
Model	STR 4-22
Description	Threaded rod cutter

## LIGHTS



Material Number	2243002
Model	SL 2-22
Description	Task light



Material Number	2242904
Model	SL 6-22
Description	Area light

## CUT-OFF SAW



Material Number	2251367
Model	DSH 600-22
Description	Hand-held battery cut-off saw



**Something big  
is landing soon**

Find out how our batteries, chargers, and portable power stations are designed to provide our tools with higher performance and run time



## SPECIALTY TOOLS



Material Number	2315589
Model	DWP 15-22
Description	Water supply tank



Material Number	2352792
Model	NCV 4-22
Description	Compact concrete vibrator



Material Number	2352088
Model	NCV 10-22
Description	Concrete vibrator backpack



Material Number	2250112
Model	RT 6-22
Description	Cordless riveting tool



Material Number	2352717
Model	NBL 4-22
Description	Cordless blower



Material Number	2333230
Model	NMX 6-22
Description	Cordless mixer



Material Number	2352771
Model	NHG 6-22
Description	Cordless heat gun



Material Number	2248354
Model	SD 5000-22
Description	Cordless drywall screwdriver

## CORDLESS ACTUATED NAILERS



Material Number	2253770
Model	BX 3-ME-22
Description	Cordless fastener

## ADHESIVE DISPENSERS



Material Number	2250851
Model	HDE 500-22
Description	Cordless dispenser

## VACUUM CLEANERS



Material Number	2415328
Model	VC 4LX-22 & T8
Description	Cordless vacuum cleaner

## LAYOUTS



Material Number	2390114
Model	PM 50MG-22
Description	Multiline laser (green)



Material Number	2399575
Model	PR 4-22
Description	Rotating laser



Material Number	2399621
Model	PR 40G-22
Description	Rotating laser (green)

## BATTERY PACKS



Material Number	2251347
Model	B 22-55 Li-ion
Description	Battery



Material Number	2251351
Model	B 22-85 Li-ion
Description	Battery



Material Number	2251359
Model	B 22-170 Li-ion
Description	Battery



Material Number	2251363
Model	B 22-255 Li-ion
Description	Battery

## BATTERY CHARGERS



Material Number	2316496
Model	C 4-22 230V
Description	Charger



Material Number	2254427
Model	C 6-22 230V
Description	Charger



Material Number	2260060
Model	C 8-22 230V
Description	Charger

It's sometimes not about size. Hilti compact tools deliver true professional performance in a lighter form. Ideal for hard-to-reach spaces, they're engineered for pros who demand precision, comfort and durability without the extra weight.



# Power tools

## DRILL DRIVERS



Material Number	2234180
Model	UD 4
Description	Drill Driver

## ANGLE GRINDERS



Material Number	2075660
Model	AG 100-8S
Description	Angle Grinder 4"

### Deadman Switch



Material Number	2075661
Model	AG 100-8D
Description	Angle Grinder 4"



Material Number	2369715
Model	AG 125-20SE
Description	Angle Grinder 5"

### Deadman Switch



Material Number	2369704
Model	AG 125-20D
Description	Angle Grinder 5"



Material Number	2075675
Model	AG 180-20P
Description	Angle Grinder 7"

### Deadman Switch



Material Number	2075676
Model	AG 180-20D
Description	Angle Grinder 7"

## ROTARY HAMMERS



Material Number	3828596
Model	TE 2
Description	Rotary Hammer SDS Plus



Material Number	3828598
Model	TE 3-CL
Description	Rotary Hammer SDS Plus



Material Number	3836534
Model	TE 6-CL
Description	Rotary Hammer SDS Plus

## COMBIHAMMERS



Material Number	3828601
Model	TE 30-AVR
Description	Combihammer SDS Plus



Material Number	3558856
Model	TE 50-AVR
Description	Combihammer SDS Max



Material Number	3748923
Model	TE 70-ATC/AVR
Description	Combihammer SDS Max

## BREAKERS



Material Number	3852663
Model	TE 500-AVR
Description	Breaker 5kg SDS Max



Material Number	5006792
Model	TE 600-AVR
Description	Breaker 6 Kg SDS Max



Material Number	3823740
Model	TE 800-AVR
Description	Breaker 10kg TE-S end



Material Number	3823741
Model	TE 1000-AVR
Description	Breaker 12kg TE-S end



Material Number	3823742
Model	TE 2000-AVR
Description	Breaker 20kg TE-S end



Material Number	3810558
Model	TE 3000-AVR
Description	Breaker 30kg TE-H end



### Lease your tools on Fleet Management

If you already lease your vehicles, you can now easily lease construction equipment with Hilti Fleet Management. For a monthly fee, you get state-of-the-art tools and a full service package that includes everything from free repairs to theft coverage with our tool lease. This means you can focus on the real business of running your jobsites more effectively.



Active Torque Control (ATC) prevents a tool body from turning in an uncontrolled manner, for example, if the tool is stuck.



Active Vibration Reduction (AVR) reduces vibration by up to two-thirds compared to conventional tools, allowing them to be used for longer and more comfortably.

# Diamond coring and cutting tools

## CORING DRILLS



Material Number	2043845
Model	DD 30-W 230V
Description	Hand-held coring up to 1-3/8"



Material Number	3613064
Model	DD 120 230V
Description	Rig-based coring up to 6"



Material Number	3612437
Model	DD 160 230V
Description	Rig-based coring up to 7"



Material Number	3550076
Model	DD 200 230V BL
Description	Rig-based coring up to 18" with easy release chuck



Material Number	3550077
Model	DD 200 230V BS
Description	Rig-based coring up to 18"



Material Number	3549991
Model	DD 350-CA BS 230V
Description	Rig-based coring up to 19-11/16"



Material Number	2051335
Model	DD-ST 30
Description	Vacuum drilling stand for DD 30-W



Material Number	2203157
Model	DD-ST 160 SFL
Description	Vacuum drilling stand for DD 160



Material Number	2027859
Model	DD-ST-VBP 120/160
Description	Vacuum baseplate for DD 120



Material Number	305538
Model	DD-HD30-VBP
Description	Vacuum baseplate for DD 200



Material Number	2082528
Model	DD AF-CA 220-480V
Description	Cut assist autofeed unit for DD 350-CA



Material Number	305903
Model	DD-BL-ET 300
Description	Core bit extension



Material Number	202899
Model	DD-BS-ET 500 S
Description	Core bit extension

## CORING ACCESSORIES



Material Number	408458
Model	DD VP-U 230V
Description	Vacuum pump for coring



Material Number	2203159
Model	DD-ST 120 SFL
Description	Drilling stand for DD 120



Material Number	2203156
Model	DD-ST 160 CTL
Description	Drilling stand for DD 160



Material Number	2148548
Model	DD-HD 30
Description	Drilling stand for DD 200 and DD 350



Material Number	305539
Model	DD-HD30-SP
Description	Spacer for DD-HD30



Material Number	000000
Model	SP-H Abrasive
Description	430 mm core bit with longer lifetime and speed



Material Number	000000
Model	P-U Abrasive Diamond core bit 430mm
Description	Standard 430 mm core bit with change module



Material Number	000000
Model	UCL DD-CM change module
Description	Change module for P-U core bit



Material Number	000000
Model	SPX-T Abrasive
Description	Core bits for DD 30-W

## WATER MANAGEMENT SYSTEM AND WATER SUPPLY



Material Number	3588722
Model	DD-WMS 100
Description	Water management supply and filtration of wastewater



Material Number	365595
Model	DWP 10
Description	Water supply unit



Material Number	2315589
Model	DWP 15-22
Description	Cordless water supply unit

## HAND-HELD CUT-OFF SAWS



Material Number	3656161
Model	DCH 300-X 230V
Description	Rig-based coring up to 18"



Material Number	2251367
Model	DSH 600-22
Description	Rig-based coring up to 19-11/16"



Material Number	2117966
Model	Cutting disc EQD SPX 305/22 univ
Description	Rig-based coring up to 19-11/16"



Material Number	2117878
Model	Cutting disc SP-S 305/22 univ
Description	Rig-based coring up to 19-11/16"



Material Number	2287945
Model	DD 350-CA BS 230V
Description	Dia blade 300/25 SPX univ A


## CONCRETE SLITTING TOOLS



Material Number	3795789
Model	DCH 150-SL 230V
Description	Slitting machine upto 50 mm width and depth



Material Number	2194554
Model	Cutting disc EQD SPX-SL 150
Description	Ultimate cutting disc for slitting machine



Material Number	2117966
Model	Cutting disc SP-SL 150
Description	Standard cutting disc for slitting machine

## CONCRETE GRINDINGS



Material Number	3810005
Model	DGH 130 230V
Description	5" Diamond concrete grinder (wall and overhead)



Material Number	3795790
Model	DGH 150 230V
Description	6" Diamond concrete grinder (floor)



Material Number	2357233
Model	Diamond cup wheel SPX turbo
Description	Ultimate diamond cup wheel 125/5"



Material Number	2238589
Model	Diamond cup wheel SPX
Description	Ultimate diamond cup wheel 125/5"



Material Number	2238569
Model	Diamond cup wheel SP
Description	Standard diamond cup wheel 125/5"



Material Number	2270778
Model	Diamond cup wheel SPX
Description	Ultimate diamond cup wheel 150/6"



Material Number	2270820
Model	Diamond cup wheel SPX fine
Description	Ultimate diamond cup wheel 150/6" for finishing grinding




Material Number	2270820
Model	Diamond polishing disc 130 SPX (50,100,200)
Description	Smooth concrete finishing without scratch marks



Material Number	2238579
Model	Diamond cup DG-CW 100/20 P (6) univ
Description	Standard diamond cup wheel 100/4"



Material Number	2163720
Model	Diamond cup 180/7" SPX (6) univ
Description	Standard diamond cup wheel 180/7"



### Tool repair made easy

We design our tools to be sturdy, but if something does go wrong, it's never been easier to book your Hilti tool in for a repair. Simply log in to your Hilti account, fill out a few details and we'll take care of the rest.

Our mission is to help you have your tools and equipment ready to work when you are. That's why we offer industry-leading warranty conditions and tool repair turnarounds at our service centre, 24/7 online booking and full tracking of your repair.

# Dust management system

## VACUUM CLEANERS



Material Number	2411684
Model	VC 40LX 220-240V
Description	Construction dust extractor



Material Number	2415328
Model	VC 4LX-22 T8
Description	Construction dust extractor



Material Number	2305016
Model	Backpack VC 3/4-T8
Description	Backpack accessory for VC 4LX-22



Material Number	436058
Model	Filter VC 20/40/150 performance
Description	Vacuum cleaner filters for wet and dry applications with additional PTFE coating



Material Number	2121386
Model	Filter VC 20/40 dry
Description	Vacuum cleaner filters for wet and dry applications with additional PTFE coating

## HEAVY DIAMOND SAWINGS



Material Number	3907926
Model	DST 20-CA 3x400V EC
Description	Wall saw with cut-assist



Material Number	2192258
Model	DSW 1510-CA 3x400V
Description	Wire saw with cut-assist



Model	Wall saw blade
Description	Wall saw blade for high speed and a long lifetime in reinforced concrete



Material Number	2276137
Model	Overvoltage protector DS-OVP 32-400
Description	Overvoltage protector for wall and wire saws



**Keep track. Increase productivity. Save money.**

Get real-time tracking, automated alerts and reporting for maintenance needs, and even track your heavy equipment with our ON!Track resource management solution.

Scan the code to begin tracking your assets >



# Measuring & detection tools

## LAYOUTS



Material Number	2441179
Model	PM 50MG-22
Description	Nuron green multiline laser



Material Number	3905453
Model	PM 30-MG
Description	Green multiline laser



NEW

Material Number	3964536
Model	PR 4-22
Description	Horizontal red rotating laser



NEW

Material Number	3964537
Model	PR 40G-22
Description	Universal green rotating laser



Material Number	378663
Model	PA 921
Description	Adjustable crank tripod

## COMBINATION LASERS



Material Number	3941061
Model	PM 20-CG A12
Description	Cross line laser



Material Number	3941062
Model	PM 20-CG AA
Description	Cross line laser

## SCANNERS AND DETECTIONS



Material Number	3905422
Model	PS 300
Description	Concrete ferros scanner

## LASER METERS









Material Number	2190182
Model	PD-S
Description	Simple distance and area measuring





Material Number	2061409
Model	PD-E
Description	Outdoor laser meter with viewfinder

## DRILL BITS




	<b>Premium</b>	
	Model	TE-C
	Description	SDS Plus Drill Bit 2 cutters
	<b>Ultimate</b>	
	Model	TE-CX
	Description	SDS Plus Drill Bit 4 cutters
	<b>Ultimate</b>	
	Model	TE-CD
	Description	SDS Plus Hollow Drill Bit
	<b>Premium</b>	
	Model	TE-Y
	Description	SDS Max Drill Bit 2 - 2 cutters
	<b>Ultimate</b>	
	Model	TE-YX
	Description	SDS Max Drill Bit 4 - 6 cutters
	<b>Ultimate</b>	
	Model	TE-YD
	Description	SDS Plus Hollow Drill Bit

## SDS PLUS CHISEL BITS

	<b>Standard</b>	
	Model	TE-C SM
	Description	SDS Plus Pointed Chisel Bit
	<b>Ultimate</b>	
	Model	TE-CX SM
	Description	SDS Plus Pointed Chisel Bit
	<b>Standard</b>	
	Model	TE-C FM
	Description	SDS Plus Flat Chisel Bit
	<b>Ultimate</b>	
	Model	TE-CX FM
	Description	SDS Plus Flat Chisel Bit
	<b>Standard</b>	
	Model	TE-C SC
	Description	SDS Plus Scaling Chisel Bit
	<b>Ultimate</b>	
	Model	TE-CX SC
	Description	SDS Plus Scaling Chisel Bit







## HEX17 CHISEL BITS

Applied for TE 500X

	<b>Standard</b>	
	Model	TE-H17 SM
	Description	Hex17 Pointed Chisel Bit
	<b>Ultimate</b>	
	Model	TE-HX17 SM
	Description	Hex17 Pointed Chisel Bit
	<b>Standard</b>	
	Model	TE-H17 FM
	Description	Hex17 Flat Chisel Bit
	<b>Ultimate</b>	
	Model	TE-HX17 FM
	Description	Hex17 Flat Chisel Bit
	<b>Ultimate</b>	
	Model	TE-HX17 SC
	Description	Hex17 Scaling Chisel Bit





## SDS MAX CHISEL BITS

Applicable for TE 500-AVR, TE 500-22, TE 600-AVR

	<b>Standard</b>	
	Model	TE-Y SM
	Description	SDS Max Pointed Chisel Bit
	<b>Ultimate</b>	
	Model	TE-YX SM
	Description	SDS Max Pointed Chisel Bit
	<b>Standard</b>	
	Model	TE-Y FM
	Description	SDS Max Flat Chisel Bit
	<b>Ultimate</b>	
	Model	TE-YX FM
	Description	SDS Max Flat Chisel Bit
	<b>Premium</b>	
	Model	TE-Y BT
	Description	SDS Plus Bushing Tool
	<b>Ultimate</b>	
	Model	TE-YX SC
	Description	SDS Max Scaling Chisel Bit






## S-END CHISEL BITS

Applicable for TE 500-AVR, TE 500-22, TE 600-AVR TE 800-AVR, TE 1000-AVR  
TE 2000-AVR TE 2000-22



Standard	
	Model TE-S SM Description S End Pointed Chisel Bit
Ultimate	
	Model TE-SX SM Description S End Pointed Chisel Bit
Ultimate	
	Model TE-SX FM Description S End Flat Chisel Bit
Standard	
	Model TE-S SC Description S End Scaling Chisel Bit

## HEX28 CHISEL BITS




Applicable for TE 3000-AVR

Standard	
	Model TE-H SM Description Hex28 Pointed Chisel Bit
Ultimate	
	Model TE-HX SM Description Hex28 Pointed Chisel Bit
Standard	
	Model TE-H FM Description Hex28 Flat Chisel Bit
Ultimate	
	Model TE-HX FM Description Hex28 Flat Chisel Bit
Standard	
	Model TE-H SC Description Hex28 Scaling Chisel Bit

## IMPACT SOCKETS

	Model SI-S 3/8" Description Impact socket SI-S 3/8"
	Model SI-S 1/2" Description Impact socket SI-S 1/2"


## DRILL BITS

	Model Hole saw 51mm-2" Description Hole saw 51mm-2" carbide tipp
	Model HSS Description Twist drill bit HSS
	Model HSS Co Description Twist drill bit HSS Cobalt

## CUTTING DISCS

Premium	
	Model AC-D SP 105x1.0 Description Angle Grinder 4" Cutting Disc
Premium	
	Model AC-D SP 125x1.0 Description Angle Grinder 5" Cutting Disc
Ultimate	
	Model AC-D SPX 125x1.0 Description Angle Grinder 5" Cutting Disc
Premium	
	Model AC-D SP 180x2.5 Description Angle Grinder 7" Cutting Disc

## FLAPPING DISCS

Premium	
	Model AF-D 125 P80 FT SP Description Angle Grinder 5" Flapping Disc

## GRINDING WHEELS

Premium	
	Model AG-D SP 100x6.4 Description Angle Grinder 4" Grinding Wheel
Premium	
	Model AG-D SP 125x6.4 Description Angle Grinder 5" Grinding Wheel
Ultimate	
	Model AG-D SPX 125x6.4 Description Angle Grinder 5" Grinding Wheel
Premium	
	Model AG-D SP 180x6.4 Description Angle Grinder 7" Grinding Wheel

## CIRCULAR SAW BLADES



Applicable for SC 4MR-22

Model	SCBM XCut Struct 136
Description	X-Cut Structural Stainless & Steel Circular Saw Blad



Applicable for SC 6ML-22

Model	SCBM XCut Struct 165 A
Description	X-Cut Structural Stainless & Steel Circular Saw Blade



Applicable for SC 6ML-22

Model	SCBM MU Steel 165
Description	Steel Circular Saw Blade



Applicable for SC 6ML-22

Model	SC-C MS 165 AL
Description	Non-Ferrous Metal Circular Saw Blade



Applicable for SC 6WL-22

Model	CBW WU SPX 165 A
Description	Wood Circular Saw Blade

## RECIP. SAW BLADES



Model	SPX univ
Description	Recip. Saw Blade Universal



Model	SP metal
Description	Recip. Saw Blade Metal

## JIG SAW BLADES



Model	GP 5
Description	Jig Saw Blade Double Curve



### Dedicated on-site support

Hilti has a long-standing tradition of sending account managers on the road to be on-site with you, aligned with our goal of being your best partner for productivity, safety and sustainability. This approach goes beyond transactional sales; it ensures that Hilti experts are present where work happens, providing immediate support, tailored solutions and proactive advice. Our account managers gain firsthand insight into your challenges, enabling them to recommend the right tools, technologies and services to help achieve your goals.



## Dedicated on-site support

### Pack it

Get all your gear to the jobsite faster with our large- capacity, flexible storage system.

### Stack it

One-handed stacking and unstacking of ProKit cases plus auto-latch lids to prevent spills.

### Track it

Get remote tracking of your ProKit storage items when you add ON!Track asset tags.

## Coming Soon