



DIAMANT BOHREN PORTFOLIO

Diamant Bohr Geräte Bohrkronen

	 DD 30-W	 DD 110 D	 DD 110 W	 DD 120	 DD 150-U-22	 DD 150-U	 DD 160	 DD 250-CA	 DD 350-CA	 DD 500-CA
 SPX-L handheld SC 68; 81 mm			 68; 81		 68; 81	 68; 81				
 SPX-L mas/ mas PC 68; 82; 107 mm		 68; 82	 68; 82		 68; 82	 68; 82; 107				
 SPX-A speed 37-162 mm					 52-162  52-250					
 SPX-T/T abrasive 8-35 mm	 8-35									
 SPX-L 25-47 mm				 25-47	 25-47	 25-47	 25-47			
 SPX-L 52-202 mm				 52-132		 52-162	 52-202			
 SPX-L mas/mas speed 52-162 mm		 52-162	 52-162		 52-162	 52-162				
 SP-L handheld 8-35 mm			 25-35		 8-35	 8-35				
 SP-L univ 37-202 mm		 37-162	 37-162  37-132	 37-132		 37-162  37-162	 37-202			
 SP-H 18-35 mm								 18-35		
 SPX-H/SP-H/H abr 52-250 / 37-600 mm								 37-500	 52-500	 82-600
 SPX-H/SP-H speed 52-250 / 37-600 mm								 37-500	 52-500	



Handgeführt



Ständergeführt



Nassbohren



Trockenbohren

 Beton

 Ziegelmauerwerk