



HILTI

NURON RECOMMENDATION CHART 2026

Battery & Charger

Choose right to improve productivity





CHOOSE THE RIGHT NURON BATTERY FOR YOUR JOB



Compact B 22-55

Compact and lightweight battery for light-duty tasks using Nuron tools.



Compact B 22-85

Versatile battery with good balance of weight, power, and runtime for light- and medium-duty tasks using Nuron tools.



Universal B 22-195

High-capacity battery built to boost the performance and runtime of medium- to heavy-duty Nuron tools.



Heavy Duty B 22-290

Our highest-capacity battery, built to maximize the runtime of heavy-duty Nuron tools.




Heavy Duty B 22-260

Our fastest-charging battery optimized for high-intensity work with heavy-duty Nuron tools.



Cordless without compromise



All-in-one cordless battery platform: Experience more power, flexibility, and boosted jobsite productivity with the 22V Nuron platform.

Ultimate performance: Perform your corded and gas-powered applications with convenience.



A battery for every job

Power through your projects: Conquer your tasks with batteries tailored to provide optimal power and runtime for your specific needs.

Simple tool crib management*



Stay prepared and productive with Hilti Fleet Management: The Nuron platform moves data from your tools and batteries to the cloud to help anticipate your needs and keep your projects on track.

Enhance jobsite efficiency: Optimize your tool crib and operations with location and usage data from Nuron. One battery platform leading to optimized toolpark.

* „ON!Track Ready“ software to consume the data and insights from the Nuron tools

- While ALL NURON batteries are compatible with ALL NURON tools, Hilti recommends specific batteries for each tool because they offer the best balance of performance, runtime and weight.*
- Tool, battery, and application determine the best battery and charger combination.

- C 6, C 8 and Flash chargers include fans that help cool batteries for faster charging.

* Some measuring tools do not provide enough space to fit all batteries. These tools have enough runtime for most applications using the compact batteries.


CHOOSE THE RIGHT NURON CHARGER

Cut downtime by up to 70% with Flash charging

Doing serial applications?

Need speed for serial applications?

Combine a flash charging B 22-260 battery with our C 8D/DC-22 Dual Bay Flash charger and get back to work in about 21 minutes when you use Boost Mode. That's up to 70% faster than charging a B 22-255 on a single-bay C 8 charger.



C 4-22 charger

Compact charger for light-duty applications where charging speed is not critical.



C 6-22 charger

Medium-speed charger for applications where charging speed is important but not critical.



C 8-22 charger

High-speed charger optimized for high-capacity Nuron batteries.



**C 8D/DC-22
Dual Bay Flash charger**

Our fastest Dual Bay Flash charger – charges two Nuron batteries in parallel as fast as the C 8-22 Nuron charger. **Boost Mode** – charges one heavy-duty Nuron battery to 80% up to twice as fast.

- *Batteries need to cooldown after medium and high intensity applications before they can start charging.
- C 6 and C 8 class chargers with active cooling speed up the charging process.
- C 8D/DC-22 (Boost mode) + B 22-260 enable Flash Charging, the fastest charging speed after application comparing to other Hilti chargers.

CHANGING TIMES AT AMBIENT CONDITIONS



		C8 DC-22				
		1 battery Boost mode	2 batteries Simultaneously	C 8-22	C 6-22	C 4-22
25 °C (77 °F)		Ambient temperature				
80 % charge Full charge						
Heavy duty	B 22-260 <small>FLASH CHARGING</small>	19 min 39 min	36 min 56 min	36 min 56 min	53 min 73 min	165 min 215 min
	B 22-290	21 min 41 min	40 min 62 min	40 min 62 min	63 min 98 min	180 min 234 min
Universal	B 22-195		24 min 48 min	24 min 48 min	45 min 70 min	127 min 158 min
Compact	B 22-85		30 min 60 min	30 min 60 min	30 min 60 min	52 min 85 min
	B 22-55		30 min 53 min	30 min 53 min	30 min 53 min	34 min 59 min

NOTE: Charging times were measured under controlled environment at 25 °C (77 °F), results may vary.



Choose right to maximize productivity

NURON

Tool description	Compact		Universal		Heavy Duty		Lead charger	Secondary charger	
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260				
Rotary hammers									
TE 2-22 SDS-plus cordless rotary hammer									-
TE 4-22 SDS-plus cordless rotary hammer								 C 6-22	 C 8-22
TE 6-22 SDS-plus cordless rotary hammer									
TE 8-22 SDS-plus cordless rotary hammer								 C 8-22	 C 8D/DC-22
TE 30-22 SDS-plus cordless rotary hammer								 C 8-22	-
TE 60-22 SDS-max cordless rotary hammer								 C 8D/DC-22	
TE 70-22 SDS-max cordless rotary hammer NEW								 C 8D/DC-22	-

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260		
Demolition hammers and breakers							
TE 500-22 SDS-max cordless chipping hammer							
TE 1000-22 TE-S cordless demolition hammer NEW							 C 8D/DC-22
TE 2000-22 TE-S cordless jackhammer							
TE 3000-22 TE-H cordless jackhammer NEW							

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger	
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260			
Drill drivers and screwdrivers								
SF 4H-22 Cordless hammer drill driver							 C 6-22	-
SF 6H-22 Cordless hammer drill driver								-
SF 8M-22 Cordless drill driver								-
SF 10W-22 Cordless drill driver							 C 6-22	 C 8D/DC-22
SF 30M-22 Cordless drill driver								
SD 5000-22 Cordless drywall screwdriver								 C 4-22
SBT 6-22 Cordless drill driver							 C 6-22	 C 4-22

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260		

Impact drivers and wrenches






SID 4-22 Cordless impact driver								-
SID 6-22 Cordless impact driver							C 6-22	-
SID 8-22 Cordless impact driver								
SIW 4R-22 Right-angle cordless impact wrench								
SIW 4AT-22 Cordless impact wrench								-
SIW 6AT-22 Mid-torque impact wrench								
SIW 8-22 Cordless impact wrench								
SIW 10-22 High-torque cordless impact wrench	NEW							C 8D/DC-22
SIW 20-22 High-torque cordless impact wrench	NEW							-

Recommended
 Compatible, will have low runtime for application of this tool
 Compatible, maybe too large or heavy for tool
 (-) Battery does not fit tool























Choose right to maximize productivity














NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
	0.55 kg  B 22-55	0.76 kg  B 22-85	1.33 kg  B 22-195	1.81 kg  B 22-290	1.64 kg  B 22-260		





















Concrete saws

DSH 600-22 ATC Battery-powered cut-off saw (300 mm) 						 C 8D/DC-22		
DSH 700-22 ATC Battery-powered cut-off saw (300 mm) 								
DSH 900-22-ATC NEW Battery-powered cut-off saw (360 mm) 							 C 8D/DC-22	

Diamond coring

DD 110-U-22 NEW Cordless core drill 						 C 8D/DC-22	
DD 150-U-22 Cordless core drill 							

Saws

SCN 60-22 NEW Cordless chainsaw 						 C 8D/DC-22	
SM 60-22 Cordless miter saw 							
SR 4-22 One-handed reciprocating saw 						 C 6-22	

 Recommended
  Compatible, will have low runtime for application of this tool
  Compatible, maybe too large or heavy for tool
 (-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg 	0.76 kg 	1.33 kg 	1.81 kg 	1.64 kg 		
SR 6-22 Reciprocating saw								
SR 10-22 Reciprocating saw	NEW							
SC 4MR-22 Cordless circular saw								
SC 6WL-22 Wood cutting circular saw								
SC 6WP-22 Cordless plunge saw								
SC 6ML-22 Cordless circular saw for metal								
SC 30WR-22 Wood cutting circular saw blade right								
SCT 60-22 Cordless table saw	NEW							-
SB 4-22 Portable band saw								

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Image	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260		
SB 6-22 Deep cut band saw							 C 6-22	 C 8-22
SMT 6-22 Cordless oscillating multitool							 C 6-22	 C 8-22
SJT 6-22 Cordless jigsaw T-handle							 C 6-22	 C 8-22
SJD 6-22 Cordless jigsaw D-handle							 C 6-22	 C 8-22
SCO 6-22 Cut-out tool							 C 6-22	-
Grinders and sanders								
AG 4D-22-125 Cordless angle grinder								
AG 4S-22-125 Cordless angle grinder							 C 6-22	 C 8-22
AG 5D-22 Cordless angle grinder (125 mm)								

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Image	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260		
AG 6D-22 Cordless angle grinder (125 mm)								-
AG 6D-22 Cordless angle grinder (150 mm)								-
DGH 130-22 Cordless concrete grinder								
GDG 6-22 Cordless die grinder								
Direct fastening tools								
BX 4-ME-22 (M&E edition) Cordless concrete nailer								

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg		
		B 22-55	B 22-85	B 22-195	B 22-290	B 22-260		
BX 4-IF-22 (IF edition) Cordless concrete nailer								
BX 3-L-22 (longer nails) Cordless concrete nailer							C 6-22	C 4-22
Specialty power tools								
NRC 6-22 Cordless rebar cutter								
RT 6-22 Cordless rivet tool								
STR 4-22 Cordless threaded rod cutter								
NHG 6-22 Cordless heat gun								
NCV 4-22 Cordless concrete vibrator								
NCV 10-22 Backpack concrete vibrator								
NMX 6-22 Cordless paddle mixer								

Recommended

Compatible, will have low runtime for application of this tool



























Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool





Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg		
		 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260		
NPU 100-22 Cordless knockout punch tool							 C 6-22	-
SSH 6-22 Cordless metal shears								
SPN 6-22 CN Cordless nibbler							C 6-22	C 8-22

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260		
Cable cutters and crimpers							
NUN 54-22 Cordless 6-ton cable crimper and cutter 						 C 6-22	
NUN 10K-22 Cordless hydraulic pump 						 C 8D/DC-22	
NCT 45 S-22 ACSR and guy wire cordless cable cutter 						 C 6-22	
NCT 53 C-22 Copper/aluminum cordless cable cutter 							
NCT 85 C-22 Copper/aluminum cordless cable cutter 							
NCR 120-22 12-ton cordless crimper 							

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger	
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260			
Dispensers								
HDE 500-22 Cordless adhesive dispenser							 C 4-22	 C 6-22
CD 4-22 Cordless caulking dispenser							 C 6-22	 C 4-22
Jobsite essentials								
KCF 4-22 Cordless jobsite fan							 C 8D/DC-22	-
NBL 4-22 Cordless compact jobsite blower							 C 6-22	-
NBL 6-22 Cordless blower							 C 8-22	 C 8D/DC-22
R 6-22 Jobsite radio							 C 6-22	 C 8-22
SL 2-22 LED task light							 C 4-22	 C 6-22
SL 4-22 Cordless searchlight							 C 6-22	-

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260		
SL 5-22 Cordless magnetic work light								
SL 6-22 LED construction light							 C 6-22	-
SL 10-22 Cordless tower light								
EXO T-22 Tool balancer								 C 8-22
Laser layout tools								
PM 50MG-22 Multi-line laser				-	-	-		
PR 4-22 Horizontal rotating laser level				-	-	-		
PR 40-22 Single slope rotating laser level				-	-	-	 C 6-22	 C 4-22
PR 40G-22 Single slope green rotating laser level				-	-	-		
PR 400-22 Dual slope rotary laser level	NEW			-	-	-		

Recommended
 Compatible, will have low runtime for application of this tool
 Compatible, maybe too large or heavy for tool
 (-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.81 kg B 22-290	1.64 kg B 22-260		
Construction vacuums and dust extractors							
PC 2-22 Cordless pressure cleaner 						 C 6-22	
VC 2D-22 Cordless construction vacuum 						 C 8D/DC-22	
VC 4HX-22 T15 Cordless H-Class dust extractor 							
VC 4MX-22 T8 Cordless M-Class dust extractor 							
VC 4MX-22 T15 Cordless M-Class dust extractor 							
DWP 15-22 Cordless water tank 							
DD WMS 100-22 Cordless water management system 							

Recommended

Compatible, will have low runtime for application of this tool











Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger
	0.55 kg  B 22-55	0.76 kg  B 22-85	1.33 kg  B 22-195	1.81 kg  B 22-290	1.64 kg  B 22-260		
DD VP WCS-22 Water collector system  			-	-	-	 C 6-22	-

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool