



NURON RECOMMENDATION CHART 2026

Battery & Charger

Choose right to improve productivity



Battery recommendation

CHOOSE THE RIGHT NURON BATTERY FOR YOUR JOB



Compact B 22-55

Compact and lightweight battery for light-duty tasks using Nuron tools.



Compact B 22-85

Versatile battery with good balance of weight, power, and runtime for light- and medium-duty tasks using Nuron tools.



Universal B 22-195

High-capacity battery built to boost the performance and runtime of medium- to heavy-duty Nuron tools.



Heavy Duty B 22-290

Our highest-capacity battery, built to maximize the runtime of heavy-duty Nuron tools.



Heavy Duty B 22-260

Our fastest-charging battery optimized for high-intensity work with heavy-duty Nuron tools.



Cordless without compromise



All-in-one cordless battery platform: Experience more power, flexibility, and boosted jobsite productivity with the 22V Nuron platform.


Ultimate performance: Perform your corded and gas-powered applications with convenience.



A battery for every job

Power through your projects: Conquer your tasks with batteries tailored to provide optimal power and runtime for your specific needs.

Simple tool crib management*



Stay prepared and productive with Hilti Fleet Management: The Nuron platform moves data from your tools and batteries to the cloud to help anticipate your needs and keep your projects on track.

Enhance jobsite efficiency: Optimize your tool crib and operations with location and usage data from Nuron. One battery platform leading to optimized toolpark.

* „ON!Track Ready“ software to consume the data and insights from the Nuron tools

- While ALL NURON batteries are compatible with ALL NURON tools, Hilti recommends specific batteries for each tool because they offer the best balance of performance, runtime and weight.*
- Tool, battery, and application determine the best battery and charger combination.

- C 6, C 8 and Flash chargers include fans that help cool batteries for faster charging.

* Some measuring tools do not provide enough space to fit all batteries. These tools have enough runtime for most applications using the compact batteries.

NURON


CHOOSE THE RIGHT NURON CHARGER

Cut downtime by up to 70% with Flash charging

Doing serial applications?

Need speed for serial applications?

Combine a flash charging **B 22-260** battery with our **C 8D/DC-22 Dual Bay Flash charger** and get back to work in about 21 minutes when you use Boost Mode. That's **up to 70% faster** than charging a B 22-255 on a single-bay C 8 charger.



C 4-22 charger

Compact charger for light-duty applications where charging speed is not critical.



C 6-22 charger

Medium-speed charger for applications where charging speed is important but not critical.



C 8-22 charger

High-speed charger optimized for high-capacity Nuron batteries.



**C 8D/DC-22
Dual Bay Flash charger**

Our fastest **Dual Bay Flash charger** – charges two Nuron batteries in parallel as fast as the C 8-22 Nuron charger. **Boost Mode** – charges one heavy-duty Nuron battery to 80 % up to twice as fast.

- *Batteries need to cooldown after medium and high intensity applications before they can start charging.
- C 6 and C 8 class chargers with active cooling speed up the charging process.
- C 8D/DC-22 (Boost mode) + B 22-260 enable Flash Charging, the fastest charging speed after application comparing to other Hilti chargers.

CHANGING TIMES AT AMBIENT CONDITIONS

		C8 DC-22		C 8-22	C 6-22	C 4-22
		1 battery Boost mode	2 batteries Simultaneously			
25 °C (77 °F)						
Ambient temperature						
Heavy duty	B 22-260	19 min 39 min	36 min 56 min	36 min 56 min	53 min 73 min	165 min 215 min
	B 22-290	21 min 41 min	40 min 62 min	40 min 62 min	63 min 98 min	180 min 234 min
Universal	B 22-195		24 min 48 min	24 min 48 min	45 min 70 min	127 min 158 min
Compact	B 22-85		30 min 60 min	30 min 60 min	30 min 60 min	52 min 85 min
	B 22-55		30 min 53 min	30 min 53 min	30 min 53 min	34 min 59 min

NOTE: Charging times were measured under controlled environment at 25 °C (77 °F), results may vary.



Choose right to maximize productivity

NURON

Tool description		Compact		Universal		Heavy Duty		Lead charger	Secondary charger
		0.55 kg  B 22-55	0.76 kg  B 22-85	1.33 kg  B 22-195	1.81 kg  B 22-290	1.64 kg  B 22-260			
Rotary hammers									
TE 2-22 SDS-plus cordless rotary hammer								 C 6-22	-
TE 4-22 SDS-plus cordless rotary hammer									 C 8-22
TE 6-22 SDS-plus cordless rotary hammer									
TE 8-22 SDS-plus cordless rotary hammer								 C 8-22	 C 8D/DC-22
TE 30-22 SDS-plus cordless rotary hammer								 C 8-22	-
TE 60-22 SDS-max cordless rotary hammer								 C 8D/DC-22	
TE 70-22 SDS-max cordless rotary hammer	 NEW							 C 8D/DC-22	-

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg		
		 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260		
Demolition hammers and breakers								
TE 500-22 SDS-max cordless chipping hammer							 C 8D/DC-22	-
TE 1000-22 TE-S cordless demolition hammer	 NEW							
TE 2000-22 TE-S cordless jackhammer								

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg		
		 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260		
Drill drivers and screwdrivers								
SF 4H-22 Cordless hammer drill driver							 C 6-22	-
SF 6H-22 Cordless hammer drill driver								-
SF 30M-22 Cordless drill driver	 NEW							 C 8D/DC-22
SD 5000-22 Cordless drywall screwdriver								 C 4-22
SBT 6-22 Cordless drill driver								

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger	
	0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg			
	 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260			
Impact drivers and wrenches								
SID 6-22 Cordless impact driver							 C 6-22	-
SIW 4R-22 Right-angle cordless impact wrench								
SIW 4AT-22 Cordless impact wrench								
SIW 6AT-22 Mid-torque impact wrench								
SIW 8-22 Cordless impact wrench							 C 8-22	 C 8D/DC-22
SIW 10-22  High-torque cordless impact wrench								-
SIW 20-22  High-torque cordless impact wrench								

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg  B 22-55	0.76 kg  B 22-85	1.33 kg  B 22-195	1.81 kg  B 22-290	1.64 kg  B 22-260		
Concrete saws								
DSH 600-22 ATC Battery-powered cut-off saw (300 mm)							 C 8D/DC-22	-
DSH 900-22-ATC NEW Battery-powered cut-off saw (360 mm)								-
Diamond coring								
DD 160-22 NEW Cordless core drill							 C 8D/DC-22	-

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger	
	0.55 kg  B 22-55	0.76 kg  B 22-85	1.33 kg  B 22-195	1.81 kg  B 22-290	1.64 kg  B 22-260			
Saws								
SR 4-22 One-handed reciprocating saw							 C 6-22	-
SR 6-22 Reciprocating saw								 C 8-22
SC 4MR-22 Cordless circular saw								
SC 6WL-22 Wood cutting circular saw								
SC 6ML-22 Cordless circular saw for metal							 C 8-22	 C 8D/DC-22
SMT 6-22 Cordless oscillating multitool							 C 6-22	 C 8-22
SJD 6-22 Cordless jigsaw D-handle								

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg  B 22-55	0.76 kg  B 22-85	1.33 kg  B 22-195	1.81 kg  B 22-290	1.64 kg  B 22-260		
Grinders and sanders								
AG 4S-22 -100 Cordless angle grinder							 C 6-22	 C 8-22
AG 4D-22-125 Cordless angle grinder								
AG 4S-22-125 Cordless angle grinder								
GDG 6-22 Cordless die grinder								
AG 6D-22 Cordless angle grinder (125 mm)							 C 8D/DC-22	-
DGH 130-22 Cordless concrete grinder							 C 8-22	 C 8D/DC-22
GDG 6-22 Cordless die grinder							 C 6-22	 C 8-22

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity



Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger	
	0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg			
	 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260			
Direct fastening tools								
BX 4-ME-22 (M&E edition) Cordless concrete nailer							 C 6-22	 C 4-22
BX 4-IF-22 (IF edition) Cordless concrete nailer								

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg  B 22-55	0.76 kg  B 22-85	1.33 kg  B 22-195	1.81 kg  B 22-290	1.64 kg  B 22-260		
Specialty power tools								
SPN 6-22 CN Cordless nibbler							 C 6-22	 C 8-22
RT 6-22 Cordless rivet tool								
STR 4-22 Cordless threaded rod cutter								
NHG 6-22 Cordless heat gun							 C 8D/DC-22	 C 8-22
NCV 4-22 Cordless concrete vibrator								-
NCV 10-22 Backpack concrete vibrator								
NMX 6-22 Cordless paddle mixer							 C 8-22	 C 8D/DC-22
EXO T-22 Tool Balancer							 C 6-22	 C 8-22

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty		Lead charger	Secondary charger	
	0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg			
	 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260			
Dispensers								
HDE 500-22 Cordless adhesive dispenser							 C 4-22	 C 6-22
CD 4-22 Cordless caulking dispenser							 C 6-22	 C 4-22
Jobsite essentials								
SL 6-22 LED construction light							 C 6-22	-
NBL 4-22 Cordless compact jobsite blower								
NBL 6-22 Cordless blower							 C 8-22	 C 8D/DC-22
SL 2-22 LED task light							 C 4-22	 C 6-22
SL 4-22 Cordless searchlight							 C 6-22	-

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg		
		 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260		
Laser layout tools								
PM 50MG-22 Multi-line laser				-	-	-	 C 6-22	 C 4-22
PR 4-22 Horizontal rotating laser level				-	-	-		
PR 40G-22 Single slope green rotating laser level				-	-	-		

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty		Lead charger	Secondary charger
		0.55 kg	0.76 kg	1.33 kg	1.81 kg	1.64 kg		
		 B 22-55	 B 22-85	 B 22-195	 B 22-290	 B 22-260		
Construction vacuums and dust extractors								
VC 2D-22 Cordless construction vacuum							 C 8D/DC-22	-
VC 4HX-22 T15 Cordless H-Class dust extractor								
DWP 15-22 Cordless water tank								

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool