



HILTI

NURON RECOMMENDATION CHART 2026

Battery & Charger

Choose right to improve productivity



CHOOSE THE RIGHT NURON BATTERY FOR YOUR JOB



Compact B 22-55

Compact and lightweight battery for light-duty tasks using Nuron tools.



Compact B 22-85

Versatile battery with good balance of weight, power, and runtime for light- and medium-duty tasks using Nuron tools.



Universal B 22-195

High-capacity battery built to boost the performance and runtime of medium- to heavy-duty Nuron tools.



Heavy Duty B 22-260

Our fastest-charging battery optimized for high-intensity work with heavy-duty Nuron tools.

Cordless without compromise



All-in-one cordless battery platform: Experience more power, flexibility, and boosted jobsite productivity with the 22V Nuron platform.

Ultimate performance: Perform your corded and gas-powered applications with convenience.



A battery for every job

Power through your projects: Conquer your tasks with batteries tailored to provide optimal power and runtime for your specific needs.

Simple tool crib management*



Stay prepared and productive with Hilti Fleet Management: The Nuron platform moves data from your tools and batteries to the cloud to help anticipate your needs and keep your projects on track.

Enhance jobsite efficiency: Optimize your tool crib and operations with location and usage data from Nuron. One battery platform leading to optimized toolpark.

* „ON!Track Ready“ software to consume the data and insights from the Nuron tools

- While ALL NURON batteries are compatible with ALL NURON tools, Hilti recommends specific batteries for each tool because they offer the best balance of performance, runtime and weight.*
- Tool, battery, and application determine the best battery and charger combination.

- C 6, C 8 and Flash chargers include fans that help cool batteries for faster charging.



* Some measuring tools do not provide enough space to fit all batteries. These tools have enough runtime for most applications using the compact batteries.

CHOOSE THE RIGHT NURON CHARGER

Cut downtime by up to 70% with Flash Charging

Doing serial applications?
Need speed for serial applications?

Combine a flash charging B 22-260 battery with our C 8D/DC-22 Dual Bay Flash charger and get back to work in about 21 minutes when you use Boost Mode. That's up to 70% faster than charging a B 22-255 on a single-bay C 8 charger.



C 4-22 charger

Compact charger for light-duty applications where charging speed is not critical.



C 6-22 charger

Medium-speed charger for applications where charging speed is important but not critical.



C 8-22 charger

High-speed charger optimized for high-capacity Nuron batteries.



C 8D/DC-22

Dual Bay Flash charger

Our fastest Dual Bay Flash charger – charges two Nuron batteries in parallel as fast as the C 8-22 Nuron charger. **Boost Mode** – charges one heavy-duty Nuron battery to 80% up to twice as fast.

- Batteries need to cooldown after medium and high intensity applications.
- C 6 and C 8 class chargers with active cooling speed up the charging process.
- C 8D/DC-22 (Boost mode) + B 22-260 enable Flash Charging, the fastest charging speed after application comparing to other Hilti chargers.

CHANGING TIMES AT AMBIENT CONDITIONS



		80 % charge Full charge		C8 DC-22		C 8-22	C 6-22	C 4-22
		1 battery Boost mode	2 batteries Simultaneously					
25 °C (77 °F)		Ambient temperature						
Heavy duty	B 22-260 <small>FLASH CHARGING</small>	19 min 39 min	36 min 56 min	36 min 56 min	53 min 73 min	165 min 215 min		
	B 22-195		24 min 48 min	24 min 48 min	45 min 70 min	127 min 158 min		
Compact	B 22-85		30 min 60 min	30 min 60 min	30 min 60 min	52 min 85 min		
	B 22-55		30 min 53 min	30 min 53 min	30 min 53 min	34 min 59 min		

NOTE: Charging times were measured under controlled environment at 25 °C (77 °F), results may vary.



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty	Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
Rotary hammers						
TE 2-22 SDS-plus cordless rotary hammer						-
TE 4-22 SDS-plus cordless rotary hammer						 C 6-22
TE 6-22 SDS-plus cordless rotary hammer						 C 8-22
TE 8-22 SDS-plus cordless rotary hammer NEW						 C8 C 8D/DC
TE 30-22 SDS-plus cordless rotary hammer						 C 8-22
TE 60-22 SDS-max cordless rotary hammer						 C 8D/DC-22
TE 70-22 SDS-max cordless rotary hammer NEW						-

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty	Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
Demolition hammers and breakers						
TE 500-22 SDS-max cordless chipping hammer						
TE 600-22 SDS-max cordless breaker NEW						
TE 1000-22 TE-S cordless demolition hammer NEW					 C 8D/DC-22	-
TE 2000-22 TE-S cordless jackhammer						
TE 3000-22 TE-H cordless jackhammer NEW						
Drill drivers and screwdrivers						
SF 4-22 Cordless drill driver					 C 6-22	-

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty	Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
SF 6H-22 Cordless hammer drill driver							-
SF 8M-22 Cordless drill driver	NEW						-
SF 30M-22 Cordless drill driver	NEW					 C 6-22	 C 8D/DC-22
SD 5000-22 Cordless drywall screwdriver							 C 4-22
SBT 6-22 Cordless drill driver							 C 4-22
Impact drivers and wrenches							
SID 4-22 Cordless impact driver						 C 6-22	-

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty	Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
SID 6-22 Cordless impact driver							-
SIW 4R-22 Right-angle cordless impact wrench						 C 6-22	
SIW 4AT-22 Cordless impact wrench							
SIW 6AT-22 Mid-torque impact wrench							
SIW 8-22 Cordless impact wrench						 C 8-22	 C 8D/DC-22
SIW 10-22 High-torque cordless impact wrench							
SIW 20-22 High-torque cordless impact wrench						 C 8D/DC	 C 8
Concrete saws							
DSH 600-22 ATC Battery-powered cut-off saw (300 mm)						 C 8D/DC-22	-
DSH 900-22-ATC Battery-powered cut-off saw (360 mm)							

Recommended Compatible, will have low runtime for application of this tool Compatible, maybe too large or heavy for tool (-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty	Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
Saws						
SR 6-22 Reciprocating saw						
SC 4MR-22 Cordless circular saw						
SC 6WL-22 Wood cutting circular saw						
SC 6WP-22 Cordless plunge saw						
SC 6ML-22 Cordless circular saw for metal						
SMT 6-22 Cordless oscillating multitool						
SJD 6-22 Cordless jigsaw D-handle						
SCO 6-22 Cut-out tool						

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty	Lead charger	Secondary charger	
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260			
Grinders and sanders							
AG 4D-22 Cordless angle grinder NEW							
AG 4S-22 Cordless angle grinder NEW							
AG 6D-22 Cordless angle grinder (125 mm) NEW							
DGH 130-22 Cordless concrete grinder							

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty	Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
Direct fastening tools							
BX 3-22 Cordless concrete nailer							
BX 4-ME-22 (M&E edition) Cordless concrete nailer						 C 6-22	 C 4-22
BX 4-IF-22 (IF edition) Cordless concrete nailer							
Diamond coring							
DD 160-22 Cordless core drill	NEW					 C 8D/DC-22	-

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description	Compact		Universal	Heavy Duty	Lead charger	Secondary charger
	0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
Specialty power tools						
RT 6-22 Cordless rivet tool						
STR 4-22 Cordless threaded rod cutter						 C 6-22
NHG 6-22 Cordless heat gun						
NCV 4-22 Cordless concrete vibrator						 C 8D/DC-22
NCV 10-22 Backpack concrete vibrator						
NMX 6-22 Cordless paddle mixer						 C 8-22

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty	Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
Cable cutters and crimpers							
NCT 45 S-22 ACSR and guy wire cordless cable cutter						 C 6-22	-
Dispensers							
HDE 500-22 Cordless adhesive dispenser						 C 4-22	 C 6-22
Jobsite essentials							
NBL 4-22 Cordless compact jobsite blower						 C 6-22	-
NBL 6-22 Cordless blower						 C 8-22	 C 8D/DC-22
SL 2-22 LED task light						 C 4-22	 C 6-22

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal	Heavy Duty	Lead charger	Secondary charger
		0.55 kg B 22-55	0.76 kg B 22-85	1.33 kg B 22-195	1.64 kg B 22-260		
SL 5-22 Cordless magnetic work light NEW							
SL 6-22 LED construction light						 C 6-22	
SL 10-22 Cordless tower light							
EXO T-22 Tool balancer							 C 8-22
Laser layout tools							
PM 50MG-22 Multi-line laser				-	-	 C 6-22	 C 4-22
PR 40-22 Single slope rotating laser level				-	-		
Construction vacuums and dust extractors							
VC 4LX-22 T8 Cordless L-Class dust extractor						 C 8D/DC-22	
DWP 15-22 Cordless water tank							

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool