



NURON RECOMMENDATION CHART 2026

Battery & Charger

Choose right to improve productivity



Battery recommendation

CHOOSE THE RIGHT NURON BATTERY FOR YOUR JOB



Compact B 22-55

Compact and lightweight battery for light-duty tasks using Nuron tools.



Compact B 22-85

Versatile battery with good balance of weight, power, and runtime for light- and medium-duty tasks using Nuron tools.



Universal B 22-110

Longer-lasting battery with extended runtime and higher power output for medium-duty tasks using Nuron tools.



Universal B 22-195

High-capacity battery built to boost the performance and runtime of medium- to heavy-duty Nuron tools.



Heavy Duty B 22-290

Our highest-capacity battery, built to maximize the runtime of heavy-duty Nuron tools.

Cordless without compromise



All-in-one cordless battery platform: Experience more power, flexibility, and boosted jobsite productivity with the 22V Nuron platform.

Ultimate performance: Perform your corded and gas-powered applications with convenience.



A battery for every job

Power through your projects: Conquer your tasks with batteries tailored to provide optimal power and runtime for your specific needs.

Simple tool crib management*



2 Years. Covered: If your Battery or Charger breaks, we'll exchange it for a new one.

Enhance jobsite efficiency: Optimize your tool crib and operations with location and usage data from Nuron. One battery platform leading to optimized toolpark.

* „ON!Track Ready“ software to consume the data and insights from the Nuron tools


- While ALL NURON batteries are compatible with ALL NURON tools, Hilti recommends specific batteries for each tool because they offer the best balance of performance, runtime and weight.*
- Tool, battery, and application determine the best battery and charger combination.

- C 6, C 8 and Flash chargers include fans that help cool batteries for faster charging.

* Some measuring tools do not provide enough space to fit all batteries. These tools have enough runtime for most applications using the compact batteries.

NURON

CHOOSE THE RIGHT NURON CHARGER



B 22-255



C 8-22



B 22-290



C 8DC-22



C 4-22 charger

Compact charger for light-duty applications where charging speed is not critical.



C 6-22 charger

Medium-speed charger for applications where charging speed is important but not critical.



C 8-22 charger

High-speed charger optimized for high-capacity Nuron batteries.



C 8D/DC-22

Dual Bay Flash charger

Our fastest Dual Bay Flash charger – charges two Nuron batteries in parallel as fast as the C 8-22 Nuron charger. **Boost Mode** – charges one heavy-duty Nuron battery to 80% up to twice as fast.

- Batteries need to cooldown after medium and high intensity applications.
- C 6 and C 8 class chargers with active cooling speed up the charging process.
- C 8D/DC-22 (Boost mode) + B 22-260 enable Flash Charging, the fastest charging speed after application comparing to other Hilti chargers.

CHANGING TIMES AT AMBIENT CONDITIONS

		 				
		C8 DC-22		C 8-22	C 6-22	C 4-22
		1 battery Boost mode	2 batteries Simultaneously			
25 °C (77 °F) Ambient temperature						
Heavy duty	 B 22-290	21 min  41 min	40 min  62 min	40 min  62 min	63 min  98 min	180 min  234 min
Universal	 B 22-195		24 min  48 min	24 min  48 min	45 min  70 min	127 min  158 min
	 B 22-110		29 min  54 min	29 min  54 min	29 min  54 min	68 min  96 min
Compact	 B 22-85		30 min  60 min	30 min  60 min	30 min  60 min	52 min  85 min
	 B 22-55		30 min  53 min	30 min  53 min	30 min  53 min	34 min  59 min

NOTE: Charging times were measured under controlled environment at 25 °C (77 °F), results may vary.



Choose right to maximize productivity

NURON

Tool description		Compact		Universal		Heavy Duty	Lead charger	Secondary charger
		0.55 kg  B 22-55	0.76 kg  B 22-85	0.91 kg  B 22-110	1.33 kg  B 22-195	1.81 kg  B 22-290		
Rotary hammers								
TE 2-22 SDS-plus cordless rotary hammer							 C 6-22	 C 8-22
TE 4-22 SDS-plus cordless rotary hammer								
TE 6-22 SDS-plus cordless rotary hammer								
TE 30-22 SDS-plus cordless rotary hammer							 C 8-22	-
TE 60-22 SDS-max cordless rotary hammer								
Demolition hammers and breakers								
TE 500-22 SDS-max cordless chipping hammer							 C 8D/DC-22	-
TE 2000-22 TE-S cordless jackhammer								

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal		Heavy Duty	Lead charger	Secondary charger
		0.55 kg	0.76 kg	0.91 kg	1.33 kg	1.81 kg		
		 B 22-55	 B 22-85	 B 22-110	 B 22-195	 B 22-290		
Drill drivers and screwdrivers								
SF 4H-22 Cordless hammer drill driver							 C 6-22	-
SF 6H-22 Cordless hammer drill driver								-
SF 10W-22 Cordless drill driver								 C 8D/DC-22
SID 6-22 Cordless impact driver								-
Impact drivers and wrenches								
SIW 4AT-22 Cordless impact wrench							 C 6-22	-
SIW 6-22 Cordless impact wrench								
SIW 6AT-22 Cordless impact wrench							 C 8-22	 C 8D/DC-22
SI-AT-22 Adaptive torque module								

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal		Heavy Duty	Lead charger	Secondary charger
		0.55 kg  B 22-55	0.76 kg  B 22-85	0.91 kg  B 22-110	1.33 kg  B 22-195	1.81 kg  B 22-290		
SIW 8-22 Cordless impact wrench							 C 8-22	 C 8D/DC-22
SIW 10-22 Cordless impact wrench								
Grinders and sanders								
SM 60-22 Cordless meter saw							 C 8D/DC-22	-
SR 6-22 Cordless reciprocating saw								
SC 6WL-22 Cordless circular saw							 C 6-22	 C 8-22
SC 6WP-22 Cordless circular saw								
SC 4MR-22 Cordless circular saw								
SJD 6-22 Cordless orbital jig saw								
AG 4S-22 Cordless angle grinder								

Recommended

Compatible, will have low runtime for application of this tool

Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal		Heavy Duty	Lead charger	Secondary charger
		0.55 kg	0.76 kg	0.91 kg	1.33 kg	1.81 kg		
		 B 22-55	 B 22-85	 B 22-110	 B 22-195	 B 22-290		
Grinders and sanders								
AG 6D-22 Cordless angle grinder							 C 8D/DC-22	-
AG 4S-22 Cordless angle grinder							 C 6-22	 C 8-22
SPN 6-22 Nibbler								
Construction vacuums and dust extractors								
NBL 4-22 Cordless blower							 C 6-22	-
SL 6-22 Cordl. area light								
50MG-22 Multi line laser PM					-	-		 C 4-22
4LX-22 Dust extractor. VC							 C 8D/DC-22	-

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool



Choose right to maximize productivity

NURON

Tool description		Compact		Universal		Heavy Duty	Lead charger	Secondary charger
		0.55 kg  B 22-55	0.76 kg  B 22-85	0.91 kg  B 22-110	1.33 kg  B 22-195	1.81 kg  B 22-290		
Direct fastening tools								
SBT 6-22 Cordless drill driver							 C 6-22	 C 4-22
BX 4-22 Battery-actuated tool								
Dispensers								
CD 4-22 Cordless dispenser							 C 6-22	 C 4-22
HDE 500-22 Cordless dispenser							 C 4-22	 C 6-22

 Recommended

 Compatible, will have low runtime for application of this tool

 Compatible, maybe too large or heavy for tool

(-) Battery does not fit tool