



Repair Cost Limit List

For the purpose of the Terms and Conditions of Repair of Hilti Power Tools, items with a no-cost warranty period of less than 2 years are classified as “Special Warranty Items”.

Tool Type	Repair Cost Limit (HKD)	No-cost Warranty Period (Year)
AG 125-15DB 04	937	1
AG 125-20D 01	710	1
AG 125-A22 02	1,041	1
AG 125-A36 02	1,080	1
AG 180-20D 03	1,058	1 year No-cost Warranty or 2 times repair (Whichever is reached earlier)
AG 230-24D 04	998	2
AG 4D-22-100 03	922	2
AG 4D-22-125 03	1,060	2
AG 4S-22-100 02	839	2
AG 4S-22-100 03	853	2
AG 4S-22-125 02	875	1
AG 4S-A22 01	723	1
AG 4S-A22-100 01	723	2
AG 5D-22-125 01	1,101	2
AG 6D-22-125 01	1,329	2
AIC 1000 01	2,000	2
BA-22 01	378	2
BX 3-BT 02	7,288	2
BX 3-IF 01	5,892	2
BX 3-L 02	6,367	2
BX 3-L-22 03	3,967	2
BX 3-ME 01	5,100	2
BX 3-ME-22 03	4,000	2
BX 3-SCT 02	7,714	2
BX 4-22 01	4,977	2
C 8-22 01	605	2
CD 4-22 02	869	2
CD 4-A22 01	884	2
DCH 300 01	6,500	2
DCH 300-X 01	4,977	2
DD 110-U-22 01	5,607	2
DD 120 01	4,259	2
DD 130 01	4,872	2
DD 150-U 01	6,165	2
DD 160 02	4,906	2
DD 160-22 01	7,056	2
DD 200 01	6,273	2
DD 200 02	5,702	2
DD 250-CA 01	5,933	2
DD 30-W 01	8,757	1
DD 350 01	23,472	2
DD 350-CA 01	16,430	2 year No-cost Warranty or 200 operating hours (Whichever is reached earlier)
DD 500-CA 01	14,605	
DD 80 01	4,127	2
DD AF-CA 01	10,237	2

Tool Type	Repair Cost Limit (HKD)	No-cost Warranty Period (Year)
DD AF-CA H 01	5,756	2
DD VP-U 01	3,150	2
DD-HD 01	4,477	2
DD-ST 120 02	793	2
DD-ST 160 03	1,446	2
DD-ST 200 02	1,860	2
DD-ST 22 01	1,955	2
DD-ST 30 01	3,378	2
DD-WMS 100 01	5,086	2
DD-WMS 100 BLE 01	5,086	2
DG 150 01	5,534	2
DGH 130 01	1,344	2
DGH 130-22 01	1,866	2
DPC 20 01	4,099	2
DPG 100 01	43,690	1
DS EB-TS20 01	72,180	1
DS RC-TS20 01	8,070	1
DS TS20-E 01	273,810	1
DSH 600-22 01	5,090	2
DSH 600-22 02	5,090	2
DSH 700-22 01	7,056	2
DSH 700-22 02	5,292	2
DSH 900-22 01	4,862	2
DSH 900RL-22 01	5,850	2
DSH-FSC 01	3,960	2
DSH-RCC 01	1,800	2
DST 10-CA 01	66,495	2 year No-cost Warranty or 200 operating hours (Whichever is reached earlier)
DST 10-CA 02	125,160	
DST 20-CA 01	200,177	
DST 20-CA 02	224,674	
DST WRC-CA 01	12,887	2
DSW 1510-CA 01	334,247	2
DSW 2005-TS 01	63,269	2
DWP 15-22 01	1,120	2
DX 2 01	1,655	1
DX 351 01	4,149	2
DX 36 01	3,153	2
DX 450 SCT 01	5,100	2
DX 460 01	3,936	2
DX 5 01	3,936	2
DX 6 01	4,000	2
DX 76 01	6,708	2
EXO-S 01	5,443	2
EXO-T-22 01	9,526	2
GDG 6-22 02	1,011	2
GX 3 01	6,814	2
HA EXO-O1 01	5,038	2
HAT 28 01	26,465	2
HDE 500-22 02	1,150	2
NBL 4-22 01	362	2
NBL 6-22 01	820	2
NCT 45 S-22 02	11,668	2

Tool Type	Repair Cost Limit (HKD)	No-cost Warranty Period (Year)
NHG 6-22 01	805	2
NMX 6-22 01	1,140	2
NPR 019 IE-A22 01	4,644	2
NPR 032 IE-A22 01	6,135	2
NPR 32-22 02	7,224	2
NRC 6-22 01	2,042	2
NUN 054 IE-A22 01	5,694	2
NUN 54-22 02	6,536	2
PC 2-22 01	781	2
PLC 600 02	26,396	2
PM 20-CG A12 01	1,900	2
PM 30-MG 01	2,214	2
PM 40-MG 01	2,214	2
PM 50MG-22 01	2,214	2
PMC 46 02	3,195	2
PR 2-HS A12 02	6,249	2
PR 30-HVS 02	6,814	2
PR 3-HVSG 02	6,880	2
PR 40-22 01	6,916	2
PR 40G-22 01	7,295	2
PS 1000 01	117,570	2
PS 200 01	35,000	2
PS 300 01	22,187	2
PS 50 01	4,482	2
PS 85 01	3,838	2
PUA 81 01	323	2
SB 4-22 02	1,171	2
SB 4-A22 01	1,089	2
SB 6-22 01	1,721	2
SBT 6-22 03	2,325	2
SC 30WR-22 01	1,738	2
SC 30WR-22 02	1,993	2
SC 4MR-22 01	1,096	2
SC 55W 01	1,119	2
SC 6ML-22 01	1,587	2
SC 6WL-22 01	1,415	2
SC 6WP-22 01	2,258	2
SC 70W-A22 01	1,591	2
SCM 22-A 01	1,326	2
SCN 60-22 01	1,789	2
SCO 6-22 02	879	2
SCO 6-A22 01	830	2
SCW 22-A 01	1,284	2
SD 5000-22 03	724	2
SD 5000-A22 02	597	2
SF 14-A 01	657	2
SF 2-A12 02	405	1
SF 2H-A12 02	467	1
SF 4-22 02	550	2
SF 4-A22 01	425	2
SF 4H-22 02	625	2
SF 6-22 03	907	2

Tool Type	Repair Cost Limit (HKD)	No-cost Warranty Period (Year)
SF 6-A22 01	720	2
SF 6-A22 02	890	2
SF 6H-22 03	982	2
SF 6H-A22 01	831	2
SF 6H-A22 02	891	2
SF BT 22-A 01	1,436	2
SFB 155 01	420	1
SFC 14-A 01	471	2
SFC 22-A 01	519	2
SFE 2-A12 01	763	1 time No-cost repair within the 1st year from purchase
SFH 14-A 01	765	2
SI-AT-22 02	1,621	2
SI-AT-A22 01	1,621	2
SID 14-A 01	828	2
SID 2-A12 02	474	1
SID 4-22 02	701	2
SID 4-A22 01	701	2
SID 4R-22 01	962	2
SID 6-22 01	869	2
SID 6-22 02	350	2
SIW 10-22 01	1,786	2
SIW 14-A 01	696	2
SIW 22-A 01	765	2
SIW 22T-A 01	1,066	2
SIW 2-A12 01	515	1
SIW 4AT-22 01	1,040	2
SIW 4R-22 01	962	2
SIW 6-22 02	1,322	2
SIW 6AT-22 03	1,322	2
SIW 6AT-A22 01	948	2
SIW 8-22 01	1,700	2
SIW 9-A22 01	1,422	2
SJD 6 DRS 02	260	2
SJD 6-22 02	1,051	2
SJD 6-A22 01	992	2
SL 10-22 01	1,769	2
SL 6-22 02	794	2
SL 6-A22 01	687	2
SMT 6-22 01	972	2
SPN 6-22 02	2,318	2
SR 2-A12 01	711	1
SR 30 01	1,295	2
SR 30-A36 01	1,179	2
SR 4-22 02	1,020	2
SR 4-A22 01	879	2
SR 6-22 02	1,436	2
SR 6-A22 01	1,293	2
SSH 6-22 02	2,899	2
ST 1800 01	1,388	1
ST 1800-A22 01	1,388	2
ST 2000-22 02	1,640	2
STR 4-22 01	2,910	2

Tool Type	Repair Cost Limit (HKD)	No-cost Warranty Period (Year)
TE 1 02	558	2
TE 1000-AVR 01	4,365	2
TE 1000-AVR 02	3,762	2
TE 1500-AVR 01	4,890	2
TE 2 02	735	2
TE 2000-22 01	4,722	2
TE 2000-AVR 01	4,287	2
TE 2-22 03	756	2
TE 2-A 01	1,143	2
TE 2-A22 02	609	2
TE 2-M 02	861	2
TE 2-S 02	723	2
TE 30 01	2,000	2
TE 30 02	1,954	2
TE 3000-AVR 01	15,828	2
TE 3000-AVR 02	16,424	2
TE 3000-AVR 03	20,106	2
TE 30-22 03	2,909	2
TE 30-A36 02	2,997	2
TE 30-A36 03	2,445	2
TE 30-AVR 01	1,845	2
TE 30-AVR 02	2,401	2
TE 30-C-AVR 01	2,103	2
TE 3-CL 01	838	2
TE 3-ML 01	870	2
TE 40 01	3,141	2
TE 40-AVR 01	3,141	2
TE 4-22 03	920	2
TE 4-A22 01	1,047	2
TE 4-A22 02	781	2
TE 50 02	3,165	2
TE 500 01	1,878	2
TE 500-22 04	3,589	2
TE 500-AVR 01	1,878	1
TE 500-AVR 03	1,878	2
TE 500-X 01	1,695	1
TE 500-X 03	1,155	1
TE 50-22 03	3,668	2
TE 50-AVR 03	2,198	2
TE 60 02	2,808	2
TE 60 03	4,077	2
TE 60-22 04	4,571	2
TE 60-22 05	5,242	2
TE 60-A36 04	4,035	2
TE 60-ATC 02	3,369	2
TE 60-ATC 03	4,881	2
TE 60-ATC-AVR 04	4,114	2
TE 60-AVR 04	4,640	2
TE 6-22 05	1,436	2
TE 6-A22 04	1,118	2
TE 6-A36 04	1,409	2
TE 6-CL 02	1,494	2

Tool Type	Repair Cost Limit (HKD)	No-cost Warranty Period (Year)
TE 6-S 01	879	2
TE 7 02	1,185	2
TE 70 02	3,642	1
TE 70-ATC 02	4,497	2
TE 70-ATC/AVR 03	6,159	2
TE 70-ATC/AVR 04	7,051	2
TE 70-AVR 03	6,017	2
TE 7-C 01	1,148	2
TE 800-AVR 01	2,528	2
TE DRS-4/6 01	477	2
VC 10L-22 01	1,711	2
VC 10M-22 01	1,711	2
VC 20-U 01	2,430	2
VC 20-UL 02	2,772	2
VC 20-UM 01	2,991	2
VC 20-UM 02	2,772	2
VC 2D-22 01	861	2
VC 40L-X 01	3,392	2
VC 40LX 05	4,266	2
VC 40M-X 01	3,392	2
VC 40MX ACD 05	4,062	2
VC 40-U 01	2,907	2
VC 40-UL 02	3,225	2
VC 40-UM 02	2,844	2
VC 40-U-Y 01	6,720	2
VC 4LX-22 01	2,599	2
VC 5-22 02	820	2
VC 5-A22 01	735	2
VC 5L 01	1,344	2
VC-CB 01	1,569	2
WSR 900-PE 01	1,473	2

Non-reparable Items

Hilti will provide replacement of these tools if the tool is damaged during the no cost warranty period, subject to the restrictions set out in the terms and conditions of repair of Hilti power tools.

Tool Type				
AI G125 01	C 4/12-50 01	KCF 4-22 01	PMA 31 01	SID 2-A 01
B 12/2.6 01	C 4/12-50 02	NPR PA 01	PMA 31G 01	SJD 6-A DRS 01
B 12/4.0 01	C 4/36-350 01	NPR PA 02	PMA 32 01	SL 2-22 02
B 12-30 01	C 4/36-DC 01	NPR PM M 01	POA 56 01	SL 2-A12 01
B 12-55 01	C 4-22 01	NPR PM V 01	POA 66 01	SL 2-A22 01
B 22/3.0 01	C 4-22 02	NPR PR M 01	POA 93 01	SL 4-22 01
B 22/4.0 01	C 6-22 01	NPR PR M 02	PRA 20 02	SMD 57 02
B 22/8.0 01	CA-B12 01	NPR PR V 01	PRA 20 04	TE 3000-T 03
B 22-110 01	CU 2-12 01	NPR PS M 01	PRA 20G 01	TE DRS-4-A 01
B 22-170 01	CU 4-22 01	NPR PS V 01	PRA 20G 04	TE DRS-6-A 02
B 22-195 01	DD-ST 120 01	PD-E 01	PRA 30 03	TE DRS-H 01
B 22-255 01	DD-ST 150-U 01	PD-S 01	PRA 30 04	TE DRS-M 01
B 22-290 01	DD-ST 160 01	PKB 16-HT 01	PRA 400 01	TE DRS-Y 01
B 22-55 01	HAT 30/50 01	PKC 19 01	PRA 84 G 01	TE-AC 2 01
B 22-85 01	HDE 500-A12 01	PKC 35 01	PSA 81 01	TU600-25 01
B 36/5.2 01	HMI 01	PKC 61 01	R 6-22 01	TU600-25 02
B 36/6.0 01	IC CDM-22 01	PKO 17 01	RC 4/36-DAB 01	TU600-25 03
B 3600 01	IC-RC 01	PKR 2 01	SFD 2-A 01	UNIVERSAL 01
BD 14/36 01	IC-RM 01	PLC 400 01	SFL 36-A 01	X-M30L B4 01

Repair Stop List

Tool Type		
AG 100-7D 03	HAT 500-C 01	PRA 84 01
AG 100-7S 03	HAT 500-P 01	PRA 90 01
AG 100-8D 03	HDE 500-A22 01	PSA 200 01
AG 100-8S 03	PLT 300 01	PSA 83 01
AG 125-13S 05	PM 2-L 01	SJT 6-A22 01
BX 3-ME 02	PM 2-LG 02	TE DRS-B 01
DD-ST HCL 01	PM 2-P 01	TE DRS-C 01
DD-ST-VBP	PM 2-PE 01	
DS WS15 02	PM 2-PG 01	
HAT 30 01	PM 4-M 01	