



WARRANTY

BEYOND THE PURCHASE

Experience the Hilti Service Difference.

Viet Nam Sep2026



The unique warranty protects tools beyond purchase

Our customer promise !

Extra benefit services !

20
YEARS

DEFECT PROTECTION

Repair or replacement for defects in materials for all HILTI Tool (Except AG 100 8S/8D is 10 years)

+1
MONTH

REPAIR QUALITY GUARANTEE

For every paid repair, your tool receives an additional 01-month warranty, free of charge.

2
YEARS

NO-COST

We will repair your tool completely free of charge for up to 2 years from the date of purchase (Except tool apply 1 year). This **includes** damage resulting from normal **wear and tear**

3–5
DAYS

PICKUP & RETURN

Third-party pickup and return within 3–5 days in urban HCM/HN.

30%
Limited

REPAIR COST CONTROL

We limit your repair cost after warranty end date. A charged repair will never cost you more than 30% of the list price at the day repair. .

FREE
SERVICE

ZERO DELIVERY COST

Pickup and return service is provided at no additional cost urban HCM/HN.

Visit hilti.vn for more detail

Corded, Laser, Diamond Coring tool

10 years

Manufacturer warranty



AG 100-8D **



AG 100-8S **



AG 230-27DB



AG 230-24D

1 year

No-cost warranty



TE 1



PM 50-MG *



PS 85*



PM 2-PE *



HDE-A12 *



PD -E *



PD -S *



C 4-12 *



B 12V *

2 years

No-cost warranty



AG 125-20SE



TE 3CL



TE 6CL



TE 30-AVR



TE 50-AVR



TE 70-AVR



TE 500-X



TE 800-AVR



TE 600-AVR



TE 1000-AVR



DD 120

2 years

No-cost warranty



TE2-22



TE 4-22



TE 6-22



TE 30-22



TE 60-22



TE 500-22



TE 2000-22



SID 6-22



SIW 4 AT-22



SIW 6AT-22



SI-AT-22 *



SR6-22



SIW 8-22



SIW 10-22



SC6 WL-22



SC 4MR-22



SM 60-22



SC 6WP-22



SJD 6-22



SPN 6-22



NBL 4-22 *



SF 4/6H-22



SBT 6-22



SF 10W-22



VC 4X-22



AG 4S-22



AG 6D-22



SL 6-22



HDE-22 *



CD 4-22 *

Batteries & chargers

No repair — Replacement warranty apply



C4



B 55



C6



B 85



C8



B 110



C8 DC-22



B 170 or 195



BX 4/ BX 3-xx



B 255 or 290

Easy access with multi channel to support you

GET STARTED BY

- 1 Hilti Online**
Submit anytime at www.Hilti.vn and track status online 24/7.
- 2 Account Manager**
Contact your Account Manager for direct consultation and support.
- 3 Technician support**
Get Technician expert troubleshooting and repair guidance.
- 4 Customer Service**
Call +84 28 3930 4091 for fast assistance.
- 5 Hilti Office or Tool service center**
Directly visit our Hilti office in HCM or Ha Noi for direct support.

You choose a channel. Hilti handles the rest!



CÔNG TY TNHH HILTI VIỆT NAM
Địa chỉ / Address: 15 Trần Khắc Chân,
Phường Tân Định, TP. HCM

Chi Nhánh Hà Nội
Tầng 1, Tòa nhà Hoàng Ngọc, Cầu
Giấy, TP Hà Nội.

Trung tâm bảo hành Hilti Việt Nam
449/89/2, Trường Chinh, Phường Tân
Bình, TP HCM.



NURON RECOMMENDATION CHART 2026

Battery & Charger

Choose right to improve productivity

HAMMER DRILL & BREAKER

			Compact		Universal		Heavy Duty
			B 55 0.55 kg	B 85 0.76 kg	B 110 0.91 kg	B 195 1.33 kg	B 290 1.81 kg
TE 2-22	Range 4–22 mm (Optimum 4–12 mm) Impact 1.5 J · W 2.3 kg						
TE 4-22	Range 4–28 mm (Optimum 4–14 mm) Impact 2.3 J · Weight 2.5 kg						
TE 6-22	Range 4–28 mm (Optimum 4–16 mm) Impact 2.6 J · W 2.8 kg						
TE 30-22	Range 5–28 mm (Optimum 10–28 mm) Impact 3.8 J · W 3.9 kg						
TE 60-22	Range 12–100 mm (Optimum 18–40 mm) Impact 8.1 J · W 6.3 kg						
TE 500-22	Chuck type TE-Y (SDS-max) Impact 8.1 J · W 6 kg						
TE 2000-22	Chuck type TE-S Impact 38.2 J · W 17.4 kg						

DRILL & IMPACT DRIVERS

			Compact		Universal		Heavy Duty
			B 55 0.55 kg	B 85 0.76 kg	B 110 0.91 kg	B 195 1.33 kg	B 290 1.81 kg
SF 4H-22	Hammer drilling & driving. ATC... Torque 36-62 Nm · W 1.4 kg						
SF 6H-22	Hammer drilling & driving. ATC... Torque 65-85 Nm · W 1.6 kg						
SF 10W-22	Drilling & driving. ATC... Torque 95-120 Nm · W 1.8 kg						
SID 6-22	Impact & Drill driving... Torque 150-300-300 Nm · W 0.9 kg						
SIW 4-AT	Impact wrench 1/2". Nut-busting 338 Nm Torque 90-135-213 Nm · W 1 kg						
SIW 6-AT	Impact wrench 1/2". Nut-busting 650 Nm Torque 300-450 Nm · W 1.8 kg						
SIW 8-22	Impact wrench 1/2". Nut-busting 1650 Nm Torque 600-1000 Nm · W 2.4 kg						
SIW 10-22	Impact wrench 3/4". Nut-busting 2000 Nm Torque 850-1600 Nm · W 2.9 kg						

CUTTINGS & GRINDINGS

			Compact		Universal		Heavy Duty
			B 55  0.55 kg	B 85  0.76 kg	B 110  0.91 kg	B 195  1.33 kg	B 290  1.81 kg
AG 4S-100	Disc 100mm, Max. cut 23 mm 6 level RPM 3400-7600 · W 1.9 kg						
AG 4S-125	Disc 125mm, Max. cut 34 mm 6 level RPM 3400-7600 · W 2.1 kg						
AG 6D-125	Disc 125mm, Max. cut 34 mm RPM 8500 · Sentech · W 2 kg						
SPN 6-22	Nibbler, max cut SS 1.5mm 16 Ga, steel sheets 2mm, C,L,U 162mm · W 2 kg						
SJD 6-22	Jigsaw, Wood, Metal, Drywall, Plastic, Aluminum , Steel · W 2.2 kg						
SC 4MR-22	Disc 125mm, Max. cut 51 mm. Metal, Steel, SS. RPM 4500 · W 2.1 kg						
SC 6WL-22	Disc 165mm, Max. cut 60 mm. None Metal. RPM 4500 · W 2.6 kg						
SC 6WP-22	Disc 125mm, Max. cut 51 mm. Metal, Steel, SS. RPM 4500 · W 2.1 kg						

OTHERS

			Compact		Universal		Heavy Duty
			B 55 0.55 kg	B 85 0.76 kg	B 110 0.91 kg	B 195 1.33 kg	B 290 1.81 kg
SR 6-22	Reciprocating saw, Max. cut 32 mm 2600 strokes/minute · W 3.1 kg						
SM 60-22	Miter Saw, Disc 305mm, Wood, Plastic RPM 4300						
SL 6-22	LED light, Brightness: 3000 lm Lux: 2100 lx @ 1 m. full day of light B 290						
SBT 6-22	Steel drilling & driving tool for installing S-BT screw-in studs RPM 2000 ·						
NBL 4-22	Blower Air volume: 186 m³/h Max. air velocity: 80.5 m/s · W 1.1 kg						
HDE-22	Dispenser with smart features for epoxy adhesive 500/330 ml.						
CD 4-22	Caulking dispenser for sealant 600/310/300ml. Expel force: 4900 N						
VC 4X-15T	Dust extractor clean ups (wet & dry), 15 L Air Flow Motor 67 l/s · W 8.9 kg						

SELECT THE CHARGER

80% CHARGE TIME at 25 °C (77 °F)		 C8 DC-22 1 battery use Boost mode 2 batteries use Simultaneously		 C 8-22	 C 6-22	 C 4-22
HEAVY DUTY B 22-290		20 min	40 min	40 min	60 min	180 min
UNIVERSAL B 22-195			24 min	24 min	45 min	127 min
COMPACT B 22-110			29 min	29 min	29 min	68 min
B 22-85			30 min	30 min	30 min	52 min
B 22-55			30 min	30 min	30 min	34 min

NOTE: Charging times were measured under controlled environment at 25 °C (77 °F); results may vary.

FULL CHARGE 100% TIME +20 to 30 min